

"my mother Nano" SERIES LINEUP

FOR DETAILS,
PLEASE
CONTACT YOUR
DEALER!

my mother Nano Standard	my mother Nano Gold	my mother Nano Premium	my mother Nano Dr.
1500cc (equivalent)	3000cc (equivalent)	6000cc (equivalent)	DOCTOR SPECIAL EDITION
DC CURRENT (A) / MAX 25A/ DC VOLTAGE (V) / MAX 4.5V	DC CURRENT (A) / MAX 34A/ DC VOLTAGE (V) / MAX 4.5V	DC CURRENT (A) / MAX 60A/ DC VOLTAGE (V) / MAX 4.5V	A SPECIAL MODEL FOR PROFESSIONAL DOCTORS WHO ARE COMMITTED TO THE SCIENCE OF HHO AND SEEK PROVEN RESULTS.
GAS TYPE HHOGAS (Atomic Hydrogen)	GAS TYPE HHOGAS (Atomic Hydrogen)	GAS TYPE HHOGAS (Atomic Hydrogen)	my mother Nano Athlete
SIZE (W*D*H) 360×240×310mm	SIZE (W*D*H) 410×270×380mm	SIZE (W*D*H) 410×270×380mm	ATHLETE SPECIAL EDITION
DRY WEIGHT APPROXIMATELY 10.0kg	DRY WEIGHT APPROXIMATELY 13.5kg	DRY WEIGHT APPROXIMATELY 18.5kg	A SPECIALLY DESIGNED MODEL DEVELOPED TO SUPPORT RECOVERY AND IMPROVE YOUR CONDITION AFTER TOUGH TRAINING.
TEMPERATURE INSIDE ELECTROLYTIC CELL 50°C	TEMPERATURE INSIDE ELECTROLYTIC CELL 50°C	TEMPERATURE INSIDE ELECTROLYTIC CELL 50°C	
OPERATING ENVIRONMENT HUMIDITY 10-30°C	OPERATING ENVIRONMENT HUMIDITY 10-30°C	OPERATING ENVIRONMENT HUMIDITY 10-30°C	
WARRANTY PERIOD 1年	WARRANTY PERIOD 1年	WARRANTY PERIOD 1年	

my mother Superior 8000cc equivalent coming soon

The next generation of HHO inhalers has been born, combining the craftsmanship of Japanese artisans with cutting-edge technology. All models are equipped with unique electrode plates and innovative technology to maximize the power of HHO. The nano-sized HHO gas generated by this technology penetrates deep into every corner of your body, helping you regain your natural glow. Choose the device that best suits your lifestyle and goals.



MANUFACTURER **Miwa Kankyo**
SOLE DISTRIBUTOR **YUKON**

MAIN OFFICE TEL : 03-5962-6077 FAX : 045-511-8309
106-0031 2-26-7 Nishiazabu, Minato-ku Tokyo

YOKOHAMA OFFICE TEL : 045-511-8308
224-0012 2-11-1 Ushikubo, Tsuzuki-ku, Yokohama, Kanagawa

ORIMOTO
MANAGEMENT CENTER 224-0043 1770 Orimotocho, Tsuzuki-ku, Yokohama, Kanagawa

NISHITOKYO FACTORY 190-1222 Hakonegasaki Higashimatsubara
Mizuho-machi, Nishitama-gun, Tokyo

MLML
HHO Inhaler "my mother"

A NEW DIMENSION OF TECHNOLOGY CALLED HHO



DOMESTIC AND INTERNATIONAL
PATENTS ACQUIRED



YOU CAN REALLY FEEL IT BECAUSE IT'S HHO NANO BUBBLES.
"my mother Nano" AWAKENS THE TRUE POWER OF YOUR BODY.

Miwa Kankyo / YUKON

COMPACT, POWERFUL AND INCREDIBLY DURABLE DRY CELL

There are two main types of electrode cell systems that generate hydrogen-oxygen gas (HHO gas): dry cell and wet cell. Most hydrogen gas generators on the market use the wet cell system. Previous research has suggested that the dry cell system is ideal for generating HHO gas. However, because implementing the dry cell system requires advanced development technology, most previous products used the wet cell system. However, thanks to the research and technological advances of our development team, we have successfully commercialized a dry cell system. This allows for both compactness and power, making it suitable for use by professionals and at home alike.

THE DIFFERENCE BETWEEN DRY AND WET CELLS

TYPE	DRY CELL	WET CELL
STRUCTURE		
MERIT	• electrolysis is carried out by passing water between the cells • lightweight (requires less water) • durable and economical due to the electrodes' resistance to damage • safe with no gas buildup	• immerse electrodes in the tank and electrolyze water • relatively easy to develop
DEMERIT	• technical capabilities are required for development	• heavy (requires a lot of water) • electrodes are constantly submerged in water, making them prone to damage and expensive to maintain • heat remains slow, and gas accumulates in the cavity above the tank (yellow area), making it unsafe

By introducing dry cell technology, we have been able to combine four requirements that were previously thought to be contradictory - "compact and powerful," "long continuous operation possible," "safety and security," and "durability and high cost performance" - into a single device. This is a new-generation inhalation machine that combines "convenience" and "power" and allows you to quickly recover your initial costs in any setting - clinic, salon, or home.

INTRODUCED IN OVER 200 CLINICS AND MEDICAL FACILITIES ACROSS JAPAN PROOF OF TRUST CHOSEN BY OVER 20 COUNTRIES AND REGIONS

TOKYO PREVENTIVE MEDICINE CLINIC
HOSHIKO CLINIC
NAKAHAMA CLINIC
MIYABI PLASTIC SURGERY
MIURA CLINIC
RYUGASAKI DAITOKU HEALTHY CLINIC

MEGUMI DENTAL CLINIC
TADA DENTAL CLINIC
ISHII DENTAL CLINIC
SONODA OSTEOPATHIC CLINIC
AKURIA DENTAL CLINIC
HEALING OFFICE
YAWARAGI ACUPUNCTURE SALON

NANTO ACUPUNCTURE AND
OSTEOPATHIC CLINIC
GINZA BIORESONANCE DENTAL
CLINIC

We also have a long history of introducing our products to clinics, treatment centers, and other overseas locations, including Russia, the UK, Kyrgyzstan, and Indonesia.

THREE FEATURES OF "my mother Nano" SERIES



ULTRA-LARGE AMOUNT OF HHO GAS + NANOBUBBLES

The Nano series has been further improved to generate atomic hydrogen and oxygen gases, as well as large amounts of fine nanobubbles (50 nm or less), which are the same size as exosomes, at high density. The newly designed electrode plates make it possible to electrolyze large amounts efficiently using less power than ever before.



ULTIMATE QUIETNESS DOUBLES COMFORT

The unique quiet design significantly reduces operating noise, allowing you to use it without disturbing those around you. Enjoy a relaxing session while maintaining a comfortable environment. It's quiet enough to read or even talk while inhaling, providing an stress-free care experience.



THOROUGH ATTENTION TO SAFETY

In addition to low-voltage operation, multiple protection circuits such as a ground fault circuit interrupter, noise filter, and overheat and overcurrent detection sensors are included as standard. Safe for long periods of continuous operation. Even in environments with small children or elderly people, any abnormalities are immediately detected to ensure safety.

CUTTING-EDGE TECHNOLOGY CREATED THROUGH DAILY STUDY

Our manufacturing and development team is made up of engineers with specialized skills in precision machinery, automobiles, and metal products. We have assembled a full-fledged team unlike any other in our industry to carry out manufacturing and development. As a result, we have already obtained patents in Japan and Taiwan, and are currently applying for patents in the United States, Europe, China, and Australia.



THE POSSIBILITIES OF HHO ARE ENDLESS WITH OPTIONAL ITEMS



HHO BATH PUMP HYDRO BUBBLE

You can easily enjoy a hydrogen bath in your own home! You can absorb HHO gas throughout your entire body.



HHO WATER GENERATING TUMBLER

You can make 500cc of hydrogen-oxygen water from mineral water or purified water in just 2 minutes!



HHO GOGGLES

The goggles are designed to apply pressure inside the goggles to make it easier to inject HHO gas into the eyeball.